


NOTES:

- 1. ALLOWABLE OPTICAL MATERIAL:  
OPTICAL GRADE GERMANIUM
- 2. CENTERING TOLERANCE (AT 587.6nm):  
BEAM DEVIATION: <3 ARCMINUTES
- 3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE

4. EDGES DIAMOND TURNED



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

|                 | S1          | S2          | EFL<br>(AT 10.6μm) | (35.00) |  Edmund Optics® |       |
|-----------------|-------------|-------------|--------------------|---------|------------------------------------------------------------------------------------------------------|-------|
| SHAPE           | CONVEX      | CONCAVE     |                    |         |                                                                                                      |       |
| RADIUS          | 38.43       | 57.61       |                    |         | TITLE                                                                                                |       |
| SURFACE QUALITY | 60 - 40     | 60 - 40     | BFL<br>(AT 10.6μm) | (33.29) |                                                                                                      |       |
| CLEAR APERTURE  | ≥ ø22.50    | ≥ ø22.50    |                    |         | ø25mm x 35mm FL, UNCOATED GERMANIUM<br>MENISCUS LENS                                                 |       |
| BEVEL MAX FACE  | 0.3mm x 45° | 0.3mm x 45° | ALL DIMS IN        | mm      | DWG NO                                                                                               | 87957 |