



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES




47664INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 6.915
GD RADIUS : 20.287
SCALE BAR : 100

REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47664INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 60.6218 μm
DIFFRACTION LIMITED RANGE: 18.423 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

47664INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656


SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47664INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



EO Edmund
optics | worldwide

www.edmundoptics.com