NOTES:

1. SUBSTRATE MATERIAL: N-BK7


- 2. ROHS COMPLIANT
- 3. SURFACE S1 TO BE PARALLEL WITH SURFACE S2 TO WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)


S1: 40% R ±5% @ 550nm 60% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm



CUT WITH 0.25mm MAXIMUM EDGE CHIP





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
ANGLE OF INCIDENCE	45°	45°	
SURFACE QUALITY	60-40	60-40	
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	

	Edmund O	ptics®

			-	
THIRD ANGLE TITLE		TITLE	Ø25mm, 40 R/60 T, PLATE BEAMSPLITTER	
ALL DIMS IN	mm	DWG NO	68385	SHEET 1 OF 1