

NOTES:



1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm

R(AVG) >96% @ 2000 - 10,000nm

S2: NONE
3. EDGES GROUND
4. RoHS COMPLIANT




FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	N/A
SURFACE FLATNESS	4 - 6λ	N/A
CLEAR APERTURE	Ø 47.50	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS INmm

 Edmund Optics®

TITLE50mm Dia Protected Gold, 4-6λ Mirror

DWG NO45615

SHEET1 OF 1