
NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH \$1 TO <30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: RAVG ≤0.4% @ 425 - 675nm



5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	20-10	20-10	THIRE PRO.		
WAVELENGTH RANGE	425 - 675nm	425 - 675nm	ALL I		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

			Edmund Option	;S®
THIRD ANGLE _ PROJECTION	$\phi \Leftrightarrow$	TITLE	12.5mm DIAMETER VIS 0° COATED, UL THIN N-BK7 WINDOW	.TRA-
ALL DIMS IN	mm	DWG NO	83101	SHEE