






NOTES:

- 1. SUBSTRATE : N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: UNCOATED  
  
S2: LASER V-COAT  
R(abs) <0.25% @ 405nm
- 3. FINE GRIND SURFACE
- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
ANGLE TOLERANCE (arcsec)	±15	±15				
SURFACE QUALITY	40-20	40-20				
SURFACE FLATNESS	λ/8	λ/8	TITLE 30mm, 405 V-COAT, N-BK7 LASER LINE RA PRISM			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm	DWG NO 83202	SHEET 1 OF 1