




NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: Ravg >98% @ 400 - 750nm
 - S2: NONE
- 4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
ANGLE TOL. (arcmin)	±2	±2				
SURFACE QUALITY	40-20	40-20				
SURFACE FLATNESS	λ/4	λ/4				
CLEAR APERTURE	90%	90%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				

THIRD ANGLE PROJECTION		TITLE	
ALL DIMS IN	mm	DWG NO	
		30mm, 400 - 750nm DIELECTRIC COATED, N-BK7 RIGHT ANGLE MIRROR	
		87392	SHEET 1 OF 1