

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)



S1: Protected Gold
R(avg) >96% @ 700 - 2000
R(avg) >96% @ 2000 - 10000nm

S2: NONE

3.

FINE GROUND SURFACE

4. RoHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	CONCAVE	CONVEX				
RADIUS	70mm	70mm				
APERTURE	f/1	N/A				
EFFECTIVE FOCAL LENGTH	35mm	N/A				
FOCAL LENGTH TOLERANCE	±2%	N/A				
SURFACE QUALITY	80-50	N/A				

THIRD ANGLE PROJECTION		TITLE		35mm Dia. x 35mm FL Protected Gold, Concave Mirror	
ALL DIMS IN	mm	DWG NO	43838	SHEET 1 OF 1	