## NOTES:

- 1. SUBSTRATE FUSED SILICA WITH CHROME DEPOSIT
- 2. OPTICAL DENSITY: >7 @ 400nm 6 @ 550nm 4.5 @ 750nm 3.6 @ 1000nm
- 3. SPECTRAL RANGE: 200 2000nm
- 4. CHECKERBOARD: 9.0 x 9.0mm² of 180 x 180 squares of 50 x 50 $\mu$ m² size PATTERN TOLERANCE: 100nm/cm = 10^-5
- 5. CONSTRUCTION: STAINLESS STEEL, 75 x 25 x 1.5mm, MICROSCOPE SLIDE FORMAT
- 6. ROHS: COMPLIANT



