





NOTES:

1. SUBSTRATE: UV FUSED SILICA
2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | VALUE |
|---------------------------------|----------------------|
| SHAPE | PLANO |
| SURFACE QUALITY | 80-50 |
| CENTER WAVELENGTH (nm) | 253.7 |
| FULL WIDTH HALF MAX (FWHM) (nm) | 25±5 |
| MIN TRANSMISSION (%) | 18 |
| CLEAR APERTURE | Ø21.00 |
| BEVEL | PROTECTIVE AS NEEDED |

EO® Edmund Optics®

| | | | |
|---------------------------|-------------|--|--------------|
| THIRD ANGLE PROJECTION | TITLE | 253.7nm, 25nm FWHM, 25mm DIA. FIRST SURFACE UV BANDPASS FILTER | |
| | ALL DIMS IN | mm | DWG NO 11991 |
| | | | SHEET 1 OF 1 |