




NOTES:

- 1. SUBSTRATE: B270
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: R(AVG) ≤ 1.50% @ 632.8nm (N-BK7)

 3. FINE GRIND SURFACE


- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	∅ 27.00	∅ 27.00
SURFACE FLATNESS	1λ PER 25.4mm	1λ PER 25.4mm
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE 30mm Dia., 1mm Thick, MgF2 Coated, B270 Window

DWG NO 17176 SHEET 1 OF 1