





FOCAL LENGTH (EFL): $9 \pm 0,09$
 BACK FOCAL LENGTH (BFL): $4,92$

1 BLACKENED SURFACE

SURFACE A			SURFACE B		SURFACE C			
Øe 8,1			Øe 8,1		Øe 8,1			
			CEMENT: NOA 61 OR EQUIVALENT					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 9mm Dia x 9mm FL, MgF2 Coated, Inked, Achromatic Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 65549INK		SHEET SIZE A4	SHEET 1 OF 3



1 AR COATING:

1/4 WAVE MgF2 @ 550nm
R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 6,87±0,007 CX Øe 8,1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BaSF64 704/394	R 5±0,005 CX Øe 8,1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION




ALL DIMS IN: mm


Edmund Optics®

TITLE 9mm Dia x 9mm FL, MgF2 Coated, Inked, Achromatic Lens

DWG NO 65549INK

SHEET SIZE A4
SHEET 2 OF 3



1 AR COATING:

¼ WAVE MgF2 @ 550nm
R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 5±0,005 CV Øe 8,1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF66 923/209	R 14,16±0,014 CX Øe 8,1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

9mm Dia x 9mm FL, MgF2 Coated,
Inked, Achromatic Lens

DWG NO

65549INK

SHEET SIZE
A4

SHEET
3 OF 3