NOTES:

1. SUBSTRATE MATERIAL: SCHOTT: N-BK7 517/642

EQUIVALENT SUBSTITUTIONS ALLOWED


- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: <3 arc min.
- 3. COATING(APPLY ACROSS CLEAR APERTURE)
 \$1, \$2, \$3, & \$4: 1/4 WAVE MGF2 @ 550nm
 \$5: MULTILAYER DIELECTRIC TO ACHIEVE
 R(ABS) = 70% ±5% @ 550nm
 T(ABS) = 30% ±5% @ 550nm
 R(AVG) = 70% ±10% FROM 400 TO 700nm
 T(AVG) = 30% ±10% FROM 400 TO 700nm

4. FINE GROUND SURFACE

SELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

6. PROTECTIVE BEVEL AS NEEDED

MARK IDENTIFIES BEAMSPLITTER COATED RIGHT ANGLE



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			EFL (AT 587.6nm)	NA	Edmund Optics®		
	\$1, \$2, \$3, \$4	\$5	(AT 567.6HH)				
SHAPE	PLANO	PLANO		NA	TITLE	10mm 70R/30T Standard Cube Beamsplitter	
SURFACE ACCURACY AT 632.8nm (P-V)	1/4 WAVE	1/4 WAVE	BFL (AT 587.6nm)				
SURFACE QUALITY	60 - 40	60 - 40					CLIEFT
MIN CLEAR APERTURE	9.0 x 9.0mm	13.1 x 9.0mm	ALL DIMS IN	mm	DWG NO	68535	SHEET 1 OF 1