





NOTES:



1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)  
OPTICAL DENSITY =  $1.5 \pm 10\%$  FROM 190 - 1700  
S1: COATED  
S2: COATED
4.  FINE GRIND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION P-V @ 632.8nm:  $\leq \lambda/4$
7. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



UV-VIS NEUTRAL DENSITY FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 <b>Edmund Optics®</b>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40-20	40-20		TITLE		
CLEAR APERTURE	Ø10	Ø10		OD 1.5, Ø12.5mm, UV-VIS ND FILTER		
COATING APERTURE	Ø10	Ø10		DWG NO		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		88268		
			ALL DIMS IN	mm	SHEET 1 OF 1	