

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS

#85-349 • 16mm FL • f/1.8

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS

Featuring low lens-to-lens variation and a broadband anti-reflection (AR) coating for maximum light transmission, TECHSPEC® Compact Instrumentation Imaging Lenses are ideal for a wide range of applications. An adjustable, lockable focus enables setting the best focus position prior to integrating into instrumentation, avoiding future adjustments. The wide range of fixed aperture options ensures maximum flexibility of resolution, throughput, and depth of field. These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized f/# versions to best suit your instrumentation application needs and to discuss volume requirements, please contact us.



Focal Length:	16mm
Minimum Working Distance¹:	100mm
Focus Range¹:	100mm - ∞
Length at Near Focus:	36.8mm
Length at Far Focus:	34.4mm
Filter Thread:	M22 x 0.75
Max Sensor Format:	2/3"
Camera Mount:	C-mount

Aperture (f/#):	f/1.8, Fixed
Magnification Range:	0X - 0.14X
Distortion²:	<1.25%
Object Space NA²:	0.02
No. of Elements (Groups):	7 (6)
AR Coating:	425-675nm BBAR
Weight:	37g

Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	1"	4/3"
Field of View ³	25mm - 12.8°	33.3mm - 17.1°	39.6mm - 20.2°	44.5mm - 22.7°	50.1mm - 25.2°	61.4mm - 30.9°	NA	NA

1. From front of housing 2. Fig 1 Distance: 200mm 3. Horizontal FOV on standard 4:3 sensor format

Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS

#85-349 • 16mm FL • f/1.8

MTF & DOF: f/1.8
WD: 200mm

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

www.edmundoptics.com

© COPYRIGHT 2014 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS

#85-349 • 16mm FL • f/1.8

MTF & DOF: f/1.8
WD: 500mm

TECHSPEC® COMPACT INSTRUMENTATION IMAGING LENS




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

www.edmundoptics.com