


NOTES:

- 1. SUBSTRATE:
GRADE A FINE ANNEALED
SCHOTT: N-BK7 517/642
- 2. ROHS COMPLIANT
- 3. WAVELENGTH RANGE: 350 - 2200nm
- 4. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: VIS 0°
R(AVG) ≤ 0.4% FROM 425-675nm @ 0° AOI
- 5. FINE GRIND SURFACE
- 6. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 7. IMAGE ORIENTATION: BEAM DEVIATION




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

| | S1 | S2 |
|-------------------------|--------------------------|--------------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 20 - 10 | 20 - 10 |
| MIN CLEAR APERTURE | Ø 11.25 | Ø 11.25 |
| MIN COATING APERTURE | N/A | N/A |
| POWER AT 632.8nm | 0.5 RINGS | 0.5 RINGS |
| IRREGULARITY AT 632.8nm | 0.2 RING | 0.2 RING |
| BEVEL | PROTECTIVE, AS NEEDED | PROTECTIVE, AS NEEDED |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | |
|--|--------------------------------|
|  Edmund Optics® | |
| TITLE | 12.5MM PRISM WEDGE 4 DEG VIS 0 |
| DWG NO | 35788 |
| SHEET 1 OF 1 | |

THIRD ANGLE PROJECTION



ALL DIMS IN mm