NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. CENTERING TOLERANCE (AT 1064nm): BEAM DEVIATION: ±3 arcmin

3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 1064nm \$5: Tp/Ts >1000:1 @ 1064nm TRANSMISSION >95% REFLECTION >99.5%



 $\sqrt{5.}$ ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE 61

6. PROTECTIVE BEVEL AS NEEDED

7. MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	\$1, \$2, \$3, \$4	\$5]			Edmund Opti	CS®
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	50mm, 1064nm, LASER LINE POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/4	λ/4					
SURFACE QUALITY	40-20	40-20		1		22, 41,61,211,211	CLIEFT
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	48870	SHEET 1 OF 1