



NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: Aluminum w/ Protective Overcoat
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	12.73 x 9.00	9.00 x 9.00
COATING APERTURE	12.73 x 9.00	9.00 x 9.00
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	10mm, Aluminum Coated, N-BK7 High Tolerance RA Prism		
DWG NO	32544	SHEET 1 OF 1	