


NOTES:

1. SUBSTRATE:
N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM WITH PROTECTED OVERCOAT
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

 FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | S2 |
|------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 20-10 | 20-10 |
| CLEAR APERTURE | 0.27 x 0.16 | 0.16 x 0.16 |
| COATING APERTURE | 0.27 x 0.16 | 0.16 x 0.16 |
| SURFACE FLATNESS | $\lambda/4$ | $\lambda/4$ |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



| TITLE | DWG NO | SHEET |
|--|--------|--------|
| 0.18mm, Aluminum Coated, N-BK7 Right Angle Prism | 66768 | 1 OF 1 |