





☒ + 0.486133
☒ 0.587562
☒ 0.656273



Surface: IMA

Spot Diagram

83979
 4/21/2017
 Units are μm.
 Field : 1
 RMS radius : 0.108
 GEO radius : 0.218
 Scale bar : 20
 Airy Radius: 5.731 μm. Legend items refer to Wavelengths
 Reference : Chief Ray

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

83979.ZMX
 Configuration 1 of 1



Chromatic Focal Shift

83979
 4/21/2017
 Maximum Focal Shift Range: 7.5048 μm
 Diffraction Limited Range: 150.202 μm
 Pupil Zone: 0.0000

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

83979.ZMX
 Configuration 1 of 1

OBJ: 0.0000 (deg)



☒ Diff. Limit-Tangential ☒ Diff. Limit-Sagittal ☒ 0.0000 (deg)-Tangential ☒ 0.0000 (deg)-Sagittal

Transverse Ray Fan Plot

83979
 4/21/2017
 Maximum Scale: ± 0.500 μm.
 0.486 0.588 0.656
 Surface: Image

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

83979.ZMX
 Configuration 1 of 1

Polychromatic Diffraction MTF

83979
 4/21/2017
 Data for 0.4861 to 0.6563 μm.
 Surface: Image
 Legend items refer to Field positions

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

83979.ZMX
 Configuration 1 of 1