

NOTES:



1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:  
LASER V-COAT

R(abs) <0.25% @ 405nm  
R(avg) <1.5% @ 375 - 435nm


 3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL	25±3%	 <b>Edmund Optics®</b>
SHAPE	CONVEX	PLANO	BFL	(17.74)	
RADIUS	12.96	∞	THIRD ANGLE PROJECTION 		TITLE
SURFACE QUALITY	60-40	60-40	ALL DIMS IN		25.0mm DIA X 25.0mm FL 405nm V-COAT, CYLINDER LENS
CLEAR APERTURE	∅ 24.00	∅ 24.00	mm	DWG NO	33219
COATING APERTURE	∅ 24.00	∅ 24.00			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			SHEET 1 OF 1