



1. SUBSTRATE MATERIAL:
N-BK7



- S1 & S2: VIS 0° (425-675nm)
R(AVG) ≤ 0.4% @ 425 - 675nm

4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	150.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL	148.68			
RADIUS	77.52	INFINITY		TITLE		12.5mm H X 25mm L X 150mm FL VIS 0° COATED, CYLINDER LENS	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	11.50 x 24.00	11.50 x 24.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	69726	SHEET 1 OF 1