NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT

 COATING (APPLY ACROSS CLEAR APERTURE) SURFACE MARKED G: NONE SURFACE MARKED S1, S2, S4 & S5:

R(avg) <0.25% @ 632nm @ 0° AOI

SURFACE MARKED S3:


NON-POLARIZING COATING PER FINISHED CUBE


SPECIFICATIONS LISTED BELOW

4. APPLY MARK IDENTIFYING BEAMSPLITTER COATED RIGHT ANGLE PRISM WITH PENCIL OR PERMANENT INK

5. TOLERANCES:

\$1 & \$2 BEAM DEVIATION TO BE WITHIN 2 arcmin \$4 & \$5 BEAM DEVIATION TO BE WITHIN 2 arcmin





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

AVERAGE TRANSMISSION Ts - Tp	45% ± 5% <3%			B	Edmund Option	CS®
ABSOLUTE TRANSMISSION	45% ± 10%	THIRD ANGLE PROJECTION		TITLE	12.5mm, 632nm, NON-POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/8					
SURFACE QUALITY	40-20					SHEET
CLEAR APERTURE	90 %	ALL DIMS IN	mm	DWG NO	35962	1 OF 1