



NOTES:

- 1. SUBSTRATE MATERIAL:  
N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: NONE

3. FINE GROUND SURFACE



- 4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
- 5. FOCAL LENGTH TOLERANCE:  $\pm 1\%$
- 6. PLANO AXIS WEDGE TOLERANCE:  $< 5$  ARCMIN  
POWER AXIS WEDGE TOLERANCE:  $< 5$  ARCMIN  
AXIAL TWIST ANGLE:  $< 3$  ARCMIN
- 7. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

REV. A	S1	S2
SHAPE	CONCAVE	PLANO
RADIUS	12.92	$\infty$
SURFACE QUALITY	40 - 20	40 - 20
CLEAR APERTURE	11.43 x 11.43	11.43 x 11.43
COATING APERTURE	N/A	N/A
POWER AT 632.8nm	1.5 WAVES PV	1.5 WAVES PV
IRREGULARITY AT 632.8nm	0.25 WAVE PV	0.25 WAVE PV
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

EFL	(-25.00)mm	 <b>Edmund Optics®</b>		
BFL	(-26.65)mm			
THIRD ANGLE PROJECTION 		TITLE	Lens PCV Cylinder 12.70mm x 12.70mm x - 25.00mm EFL	
ALL DIMS IN	mm	DWG NO	34758	SHEET 1 OF 1