


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM WITH PROTECTIVE OVERCOAT W/ BLACK OVERPAINT
R(AVG) > 85% FROM 400-700nm @ 45° AOI
R(AVG) > 90% FROM 400-2,000nm @ 45° AOI

S2: ¼ WAVE MgF2 @ 550nm
R(AVG) < 1.75% FROM 400-700nm (N-BK7)

3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT
- 5. TYPICAL ENERGY DENSITY: 0.3 J/cm² @ 10ns @ 532nm & 1064nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div><div></div></div><div>TITLE</div><div>45mm, Aluminum & MgF2 Coated, N-BK7 Right Angle Prism</div></div> <div><div>GO[®] Edmund Optics[®]</div><div>DWG NO</div><div>45396</div><div>SHEET 1 OF 1</div></div>				
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	45396	SHEET 1 OF 1
CLEAR APERTURE	57.24 x 40.5	40.5 x 40.5					
COATING APERTURE	57.24 x 40.5	40.5 x 40.5					
SURFACE FLATNESS	λ/4	λ/4					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					

Edmund Optics®