





- NOTES:
- COATING (APPLY ACROSS CLEAR APERTURE)
 BBAR & LASER V-COAT
 R(AVG): 0.1% @ 1940nm - 1950nm
 R(AVG): 0.5% @ 1900nm - 2100nm
 R(AVG): 0.25% @ 2000nm - 2100nm



- 2 MOUNTING THREADS:
 INPUT: MALE M30 x 1
 OUTPUT: FEMALE M27 x 0.5

3. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

DESIGN WAVELENGTH DWL (nm)	1940				
EXPANSION POWER	3X				
TRANSMISSION %	99 (nominal)				
TRANSMITTED WAVEFRONT, P-V	λ/10 FOR 5.5mm INPUT BEAM (NOMINAL, λ = DWL)				
		ALL DIMS IN	mm	TITLE	3X, 2µm Low Power Vega™ Laser Line Beam Expander
		DWG NO	37377	SHEET 1 OF 1	