






NOTES:

1. SUBSTRATE MATERIAL:  
ALUMINUM
2. FINISH (EXCEPT SURFACE S1):  
BLACK ANODIZED
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: PROTECTED ALUMINUM  
R(AVG) >85% from 0.4-0.7 $\mu$ m  
R(AVG) >97% from 2 - 12 $\mu$ m  
  
SURFACE ROUGHNESS: <100 Å RMS
4. FOCAL LENGTH TOLERANCE:  $\pm 1\%$
5. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	EFL	326.69	 Edmund Optics®		
SHAPE	PARABOLIC	PFL	304.80			
REFLECTIVE WAVEFRONT DISTORTION AT 632.8nm (RMS)	2λ	<div>THIRD ANGLE PROJECTION</div> 		TITLE	Ø101.6 X 326.69mm EFL 30° OAP PROTECTED ALUMINUM MIRROR 100Å	
SURFACE FIGURE AT 632.8nm (RMS)	1λ					
CLEAR APERTURE	90%	ALL DIMS IN	mm	DWG NO	35584	SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED					