




NOTES:

- 1. SUBSTRATE:
PMMA
- 2. COATING
S1 & S2: NONE
- 3. FOCAL LENGTH TOLERANCE: $\pm 1\%$



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | | | |
|-------|----------------------|----|----------------------|--|----|--------|---|-----------------|
| S1 | | S2 | | THIRD ANGLE PROJECTION  | | TITLE | 25.4mm DIA F/10 UNCOATED, MOLDED ACRYLIC ASPHERIC LENS | |
| SHAPE | CONVEX | | PLANO | | | | | |
| BEVEL | PROTECTIVE AS NEEDED | | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 48175 | SHEET 1 OF 1 |

 **Edmund Optics®**