

NOTES:


- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. COATING (APPLY ACROSS CLEAR APERTURE): S1: BARE ALUMINUM S2: NONE
- 3. WAVELENGTH RANGE: 250-400nm ABSOLUTE DIFFRACTION EFFICIENCY: 45-65% GROOVE DENSITY: 3600 grooves/mm



5. Rohs Compliant







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	\$1	\$2			
SHAPE	PLANO	PLANO			
CLEAR APERTURE	11.43 x 11.43	N/A			
	•	-			



THIRD ANGLE TITLE		TITLE	GRATING HOLO 3600GR UV 12.7 X 12.7	
ALL DIVACINI		DWCNO		SHEET
ALL DIMS IN	mm	DWG NO	43778	1 OF 1