



NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: NONE
  - S2: 266nm Laser AR Coating
  - R(ABS) < 0.25% @ 266nm @ 0° AOI
- DAMAGE THRESHOLD
  - PULSED: 3J/cm² @ 20ns, 20Hz @ 266nm

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	15.90 x 11.25	Ø11.25
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	12.5mm 1/20 WV 266nm AR CTD HT RA FS PRISM		
DWG NO	37618	SHEET 1 OF 1	