



NOTES:

1. SUBSTRATE MATERIAL:  
Schott 47A Glass with EMA
2. NUMERICAL APERTURE: 1
3. DISTORTION: 1%
4. CORE/CLAD RATIO: 75/25
5. RESOLUTION: 102 lp/mm  
RESOLVING POWER: 6µm
6. COEFFICIENT OF THERMAL EXPANSION CTE (10<sup>-6</sup>/°C): 6.8
7. OPERATING TEMPERATURE(°C): -10 to +300
8. ROHS: Exempt



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50

THIRD ANGLE PROJECTION	
ALL DIMS IN	mm

TITLE	FIBER OPTIC FACEPLATE, 75 X 50 X 5mm		
DWG NO	55143	SHEET	1 OF 1