


LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R	68,77±0,069 CX		GLASS	FUSED SILICA 458/678	R	∞ PL		
Øe	49				Øe	49		
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm		
4/	-				4/	2,18'		
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)		
6/	-				6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	50mm Dia, x 150mm FL 1550nm V-Coat, UV PCX Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	DWG NO	34172	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110								