



NOTES:

- 1. SUBSTRATE: FUSED SILICA
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: 266nm HR Coating
 - R(ABS) > 99.5% @ 266nm @ 45° AOI
 - R(AVG) > 99.5% FROM 263-268nm @ 45° AOI
- DAMAGE THRESHOLD
PULSED: 2.5 J/cm² , 20ns, 20 Hz @ 266nm
CW: 1MW/cm² @ 266nm

3 FINE GRIND SURFACE


- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	6.36 x 4.50	Ø4.50
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 		Edmund Optics®	
ALL DIMS IN mm		TITLE	5mm, 1/20 WAVE, 266nm, HR CTD HYP, HT RA, FS PRISM
DWG NO		37640	SHEET 1 OF 1