

NOTES:



1. SUBSTRATE
FUSED SILICA
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE):

S1: 355 HR Coating
R (ABS) > 99.80% @ 355nm @ 45° AOI
R (AVG) > 99.5% @ 351 - 358nm @ 45° AOI

DAMAGE THRESHOLD,
PULSED: 6 J/cm², 20ns, 20Hz @ 355nm
CW: 1MW/cm² @ 355nm

S2: NONE

4. FINE GRIND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES
7. APPLY ARROW ON EDGE WITH LASER ETCH, PENCIL, OR PERMANENT INK POINTING TOWARDS SURFACE S1



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION TITLE Ø50.8mm x 9.53mm, 355nm, NdYAG MIRROR 45° AOI DWG NO 38862 SHEET 1 OF 1			
SURFACE QUALITY	10-5	COMMERCIAL POLISH				
SURFACE FLATNESS	0.10 WAVE	N/A				
MIN CLEAR APERTURE	Ø40.64	N/A				
MIN COATING APERTURE	Ø45.72	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	38862

Edmund Optics®