NOTES:


1. SUBSTRATE: FLOAT GLASS


2. COATING (APPLY ACROSS CLEAR APERTURE)

\$1 & \$2: BBAR (425-700nm) Ra(AVG)≤0.5% @ 425 - 700nm

3. FINE GRIND SURFACE

4. ROHS COMPLIANT





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	S2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	80-50	80-50		
CLEAR APERTURE	Ø80.01	Ø80.01		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED		

			Edmund Option	S®
THIRD ANGLE PROJECTION		TITLE	88.9mm Dia. x 3mm High Efficiency Wi	ndow
ALL DIMS IN	mm	DWG NO	39286	SHEET 1 OF 1