





FOCAL LENGTH (EFL): $30 \pm 0,3$
 BACK FOCAL LENGTH (BFL): 28,222

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	15,505±0,016 CX		GLASS N-BK7 517/642	R	∞ PL	
Øe	11,5			Øe	11,5	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 12,5mm Dia x 30mm FL, Uncoated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				TITLE 12,5mm Dia x 30mm FL, Uncoated, Plano-Convex Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 37790	SHEET SIZE A4
						SHEET 1 OF 1