





FOCAL LENGTH (EFL): 75 ±0,75
BACK FOCAL LENGTH (BFL): 74,11

1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	68,362±0,068 CX		GLASS FUSED SILICA 458/678	R	68,362±0,068 CX	
Øe	11			Øe	11	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	2,18'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				12mm Dia, x 75mm FL, VIS 0 Coated, UV Double-Convex Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	48979
			SHEET SIZE A4			SHEET 1 OF 1