




FOCAL LENGTH (EFL): $25 \pm 0,25$
 BACK FOCAL LENGTH (BFL): $23,22$

— · — BLACKENED SURFACE

1 VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350-700nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 12,92 CX Øe 11 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 11 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12,0mm Dia, x 25,0mm FL, VIS-EXT,
 Inked, Plano-Convex Lens

DWG NO

38445INK

SHEET SIZE A4

SHEET 1 OF 1