




FOCAL LENGTH (EFL): 85 ±0,85
BACK FOCAL LENGTH (BFL): 82,17

1 AR COATING: 980nm V-COAT
R(ABS) < 0,25% @ 980nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	43,93±0,044 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
SCALE: NONE
λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

25,0mm Diameter x 85,0mm FL, 980nm V-Coat, PCX Lens

DWG NO

69569

SHEET SIZE
A4

SHEET
1 OF 1