




FOCAL LENGTH (EFL): $9 \pm 0,09$
 BACK FOCAL LENGTH (BFL): $7,95$

1 AR COATING: 1064nm V-COAT
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$6,05 \pm 0,006 CX$	GLASS N-SF5 673/322	R	∞PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8 nm$		3/	3 (0,5) $\lambda=632,8 nm$
4/	-		4/	4,46'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

6,0mm Diameter x 9,0mm FL, 1064nm V-Coat, PCX Lens

DWG NO

66266

SHEET SIZE
A4

SHEET
1 OF 1