




FOCAL LENGTH (EFL): $24 \pm 0,24$
 BACK FOCAL LENGTH (BFL): $22,15$

1 AR COATING: 1310nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 1310\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$12,42 \pm 0,012 \text{ CX}$	GLASS N-BK7 517/642	R	$\infty \text{ PL}$
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6\text{nm}$

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

12,0mm Diameter x 24,0mm FL, 1310nm
V-Coat, PCX Lens

DWG NO

84171

SHEET SIZE
A4

SHEET
1 OF 1