


LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	19,62±0,02 CX		GLASS	N-SF11 785/258	R	∞ PL	
Øe	19				Øe	19	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	1,27'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm		
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 20,0mm Diameter x 25,0mm FL, 1550nm V-Coat, PCX Lens
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm
			DWG NO	89056
			SHEET SIZE A4	
			SHEET 1 OF 1	