



NOTES:



- 1. SUBSTRATE:
D-ZLAF52LA
- 2. NUMERICAL APERTURE: 0.32
- 3. COATING
S1 & S2: NONE
- 4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
- 5. TRANSMITTED WAVEFRONT ERROR (λ , RMS): < 0.40



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø1.60	Ø1.60
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL	2.51	 Edmund Optics®		
BFL	1.76			
	TITLE	0.32 NA 2.51mm FL UNCOATED, MOLDED ASPHERIC LENS		
		DWG NO	83573	SHEET 1 OF 1
ALL DIMS IN	mm			