




NOTES:

1. TYPE OF MOVEMENT: Linear (X)
TRAVEL (mm): 26
2. TYPE OF DRIVE: Ultrasonic Motor
3. LOAD CAPACITY (kg): 2 (Horizontal)
4. RESOLUTION (um): 0.5 Typ. (Open Loop)
5. PITCH (urad): 80
YAW (urad): 80
FLATNESS (um): 1.5
6. SPEED (mm/s): 2 Max with #88-552
7. REPEATABILITY (um): Bi-directional: ± 1.0 Uni-directional: 1.0
8. NOTE - Use with Piezo Positioning Stage Controller #88-552



EO® Edmund Optics®

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

THIRD ANGLE PROJECTION		TITLE		26mm Travel Piezo Positioning Stage	
ALL DIMS IN	mm	DWG NO	88549	SHEET 1 OF 1	