




FOCAL LENGTH (EFL): 150 ± 1,5

BACK FOCAL LENGTH (BFL): 147,33

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 71,413 CX Øe 11,7 (λ) - 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ -		GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) - 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 355nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION 		
		ALL DIMS IN: mm	TITLE 12,7mm Dia x 150mm FL, Uncoated, Plano-Convex Lens	SHEET SIZE A4
			DWG NO 38639	SHEET 1 OF 1