



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




SECTION A-A

SPECIFICATION	VALUE
CENTER WAVELENGTH (CWL)	350nm \pm 5 nm
FULL WIDTH HALF MAX (FWHM)	50nm \pm 5 nm
MINIMUM TRANSMISSION	>90 %
BLOCKING	≥ 4.0 FROM 200 - 1200 nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	Hard Coated

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION 		TITLE	350nm CWL, 25mm Dia. Hard Coated OD 4 50nm Bandpass Filter	
ALL DIMS IN	mm	DWG NO	12095	SHEET 1 OF 1