





FOCAL LENGTH (EFL):  $500 \pm 5$   
 BACK FOCAL LENGTH (BFL): 497,44

- 1 266nm Laser AR Coating  
 R(ABS) < 0,25% @ 266nm @ 0° AOI

| LEFT SURFACE                                                                                                                                                                                                                                                                     |  | MATERIAL                                                                                                                         | RIGHT SURFACE                                                                                                                                                                                                                                                                                                                                |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| R 238,044 CX<br>Øe 11,7<br>(λ) SEE NOTE 1<br>3/ 2 (0,2) λ=632,8 nm<br>4/ -<br>5/ 10 - 5<br>6/ 3J-cm <sup>-2</sup> ; 266nm; 20ns [20Hz]                                                                                                                                           |  | GLASS Fused Silica 458/678                                                                                                       | R ∞ PL<br>Øe 11,7<br>(λ) SEE NOTE 1<br>3/ 2 (0,2) λ=632,8 nm<br>4/ 2,18'<br>5/ 10 - 5<br>6/ 3J-cm <sup>-2</sup> ; 266nm; 20ns [20Hz]                                                                                                                                                                                                         |  |
| PROTECTIVE CHAMFERS AS NEEDED<br>ROHS: COMPLIANT<br>SCALE: NONE<br>λ = 355nm<br>SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY<br>FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING<br>INDICATIONS IN ACCORDANCE WITH ISO 10110 |  | FIRST ANGLE PROJECTION<br><br>ALL DIMS IN: mm | <div>  <b>Edmund Optics®</b> </div> <div>           TITLE 12,7mm Dia x 500mm FL, 266nm Laser AR Coating, 3J Coated, Plano-Convex Lens<br/>           DWG NO 38669         </div> <div>           SHEET SIZE A4<br/>           SHEET 1 OF 1         </div> |  |