





FOCAL LENGTH (EFL): 50 ± 0,5
 BACK FOCAL LENGTH (BFL): 47,3

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 23,804 CX			GLASS Fused Silica 458/678	R ∞ PL		
Øe 11,7				Øe 11,7		
⌀ -				⌀ -		
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 10 - 5				5/ 10 - 5		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	EO[®] Edmund Optics[®]		
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 12,7mm Dia x 50mm FL, Uncoated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	38636
					SHEET SIZE	A4
					SHEET 1 OF 1	