



NOTES:

1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: 73
4. SAMPLED ANGLE: 4.0 x 4.0
5. COATING:  
LASER V-COAT (1064nm)
6. BEAM SPECIFICATION:  
MINIMUM BEAM DIAMETER: 0.37mm



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

|                    |                      |                      |  |  |             |  |        |
|--------------------|----------------------|----------------------|--|--|-------------|--|--------|
|                    | S1                   | S2                   | THIRD ANGLE PROJECTION  |  | TITLE       | 1064nm, 20mm Dia., 9x9 SPOT MATRIX, DIFFRACTIVE BEAMSPLITTER |        |
| SHAPE              | PLANO                | PLANO                |  |  | ALL DIMS IN | mm   | DWG NO |
| MIN CLEAR APERTURE | Ø18                  | Ø18                  |  |  |             |  |        |
| BEVEL MAX FACE     | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |  |  |             |  |        |