





FOCAL LENGTH (EFL): 1000 ±10
BACK FOCAL LENGTH (BFL): 997,59

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R 476,089 CX			GLASS Fused Silica 458/678	R ∞ PL	
Øe 11,7				Øe 11,7	
⌂ -				⌂ -	
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm	
4/ -				4/ 2,18'	
5/ 10 - 5				5/ 10 - 5	
6/ -			6/ -		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				12,7mm Dia x 1000mm FL, Uncoated, Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO	38645
				SHEET SIZE	A4